

Execute command file: F:\C31BOOT\TIMTEST.CMD

Cmd: rm 808030 9

808030: 00000008	00000008	00000008	00000008	
808034: 00000000	00000000	00000000	00000000	
808038: 00000000				

Cmd: wm 808030 200

Cmd: wm 808034 0

Cmd: wm 808038 87654321

Cmd: rm 808030 9

808030: 00000208	00000208	00000208	00000208	
808034: 00000000	00000000	00000000	00000000	
808038: 87654321	!Ce.			

Cmd: wm 808030 2C0

Cmd: rm 808030 9

808030: 00000288	00000288	00000288	00000288	
808034: 0021D702	0021D717	0021D72D	0021D742	..!...!..-..!..B..!
808038: 87654321	!Ce.			

Cmd: wt 5

Cmd: rm 808030 9

808030: 00000288	00000288	00000288	00000288	
808034: 063DDE9E	063DDEB3	063DDEC9	063DDEDE	..=...=...=...=.
808038: 87654321	!Ce.			

Cmd: wt 5

Cmd: rm 808030 9

808030: 00000288	00000288	00000288	00000288	
808034: 0C5E98F7	0C5E990D	0C5E9922	0C5E9938	..^...^...".^..8..^..
808038: 87654321	!Ce.			

Cmd: wm 808030 200

Cmd: rm 808030 9

808030: 00000208	00000208	00000208	00000208	
808034: 0C843A16	0C843A16	0C843A16	0C843A16	
808038: 87654321	!Ce.			

Cmd: wt 5

Cmd: rm 808030 9

808030: 00000208	00000208	00000208	00000208	
808034: 0C843A16	0C843A16	0C843A16	0C843A16	
808038: 87654321	!Ce.			

Cmd: **

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				

Cmd: wm 808020 200

Cmd: wm 808024 0

Cmd: wm 808028 87654321

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				

Cmd: wm 808020 2C0

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				

Cmd: wt 5

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				

Cmd: wt 5

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				

Cmd: wm 808020 200

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				

Cmd: wt 5

Cmd: rm 808020 9

808020: 00000208	00000208	00000208	00000208	
808024: 00009C55	00009C55	00009C55	00009C55	U...U...U...U...
808028: FFFFFFFF				