



Note:

1. Input capacitance of Vbus should not exceed 10uF.
2. LT1121-3.3 is 3.3V voltage regulator.
3. DS1233A is reset IC with manual reset button feature.
4. 2N3904 sets TP40 at 3.0 voltage after reset.
5. 22pF caps are used to bypass high frequency and for edge rate control (optional)

Copyright 1998, Texas Instruments Incorporated		
Title	USB2046 Self Power with External Memory	
Size B	Document Number	Rev
	98111603	
Date:	Thursday, February 11, 1999	Sheet 1 of 13