


# 411 Output vs RxCLKIn



## Channel Status

	C1	C2	C3	C4
V / Div	200 mV	200 mV	200 mV	200 mV
Offset	-800.0 mV	-800.0 mV	-1.6000 V	-1.6000 V
Coupling	DC1MΩ	DC1MΩ	DC1MΩ	DC1MΩ
BW-Limit	Full	Full	Full	Full
Probe	10	10	10	10
Sweeps	1 #	1 #	1 #	1 #

## Acquisition Status

Time / Div	10.0 ns	Sampling Rate	5.0 GS/s
Time / Pt	200 ps	Sampling Mode	RealTime
Pts / Div	50.0 S	Trigger Delay	-1.8 ns
Mode	Stop	Slope	Negative
Type	Edge	Level	1.300 V
Source	C1	Coupling	DC

