


RxCik IN +/-



#### Channel Status

	C1	C2
V / Div	200 mV	200 mV
Offset	-1.2000 V	-1.2000 V
Coupling	DC1MΩ	DC1MΩ
BW-Limit	Full	Full
Probe	10	10
Sweeps	1 #	1 #

#### Acquisition Status

	Time / Div	50.0 ns	Sampling Rate	5.0 GS/s
Horizontal	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	250.0 S	Trigger Delay	0 ns
	Mode	Stop	Slope	Negative
Trigger	Type	Edge	Level	1.274 V
	Source	C1	Coupling	DC

