


15V Lab Supply



Channel Status

		C4
Vertical	V / Div	5.00 V
	Offset	0.00 V
	Coupling	DC1MQ
	BW-Limit	Full
	Probe	10
	Sweeps	1 #

Acquisition Status

Horizontal	Time / Div	50.0 ns	Sampling Rate	10 GS/s
	Time / Pt	100 ps	Sampling Mode	RealTime
	Pts / Div	500.0 S	Trigger Delay	0 ns
Trigger	Mode	Single	Slope	Negative
	Type	Edge	Level	1.275 V
	Source	C1	Coupling	DC

