




Rs
Change the resistance
(Open, 2kΩ, 650Ω, 280Ω)

Rf
Could you please let me know best
value for achieve best THD+N?

Gain	Rf	Frequency	THD	2nd	3rd	4th	5th
	kohms	kHz	dB	dB	dB	dB	dB
1	2	20	-97	-98	-107	-112	-119
1	1	20	-100	-102	-109	-118	-118
1	0	20	-106	-107	-110	-115	-119
11	2	20	-97	-102	-100	-111	-105
11	1	20	-93	-99	-97	-103	-97

-Gain = 1

THS is better when RF value is small.

-Gain = 11

THS is better when RF value is big.