



C1	DC1M	C2	DC1M	C3	DC1M	C4	DC1M
10.0 V/div		2.00 V/div		1.00 V/div		5.00 V/div	
25.00 V ofst		2.000 V ofst		-1.000 V ofst		-15.00 V ofst	

Tbase	-1.50 s	トリガ	C2 DC
Roll	500 ms/div	停止	3.16 V
100 kS	20 kS/s	Edge	下向き