



<b>C1</b>	<b>DC1M</b>	<b>C2</b>	<b>DC1M</b>	<b>C3</b>	<b>DC1M</b>	<b>C4</b>	<b>DC1M</b>
10.0 V/div		10.0 V/div		5.00 V/div		5.00 V/div	
25.00 V ofst		10.00 V ofst		-5.00 V ofst		-14.95 V ofst	

Tbase	-60.0 ms	トリガ	<b>C1</b> <b>DC</b>
	20.0 ms/div	停止	8.5 V
1.00 MS	5.0 MS/s	Edge	上向き