

More (1 of 2)

Delete All

Measurements Markers Status Scales

50.0 μ s/ 0.0 s 0.0 V

	X	Y
A—(1) =	-105.00050000 μ s	-77.40 mV
B---(1) =	-80.00050000 μ s	21.00 mV
Δ =	25.00000000 μ s	98.40 mV
1/ΔX =	40.00000000 kHz	

DC Full	DC Full	More than
5.00 V/div	5.00 V/div	T1 1.5000ns
10:1	10:1	