




Title		
Size	Number	Revision
A3		
Date:	2014-9-19	Sheet of
File:	F:\AG1101\AD9361\5.8G原理图\CLK_Schematic	Drawn By:

Comment	Description	Designator	Footprint	LibRef	Quantity
	Capacitor, Capacitor,	C1, C2, C3, C4, C5, C6, C8, C9, C10, C11, C12, C13, C14, C15, C16, C17, C18, C19, C20, C21, C23, C24, C25, C26, C27, C28, C29, C31, C32, C33, C34, C35, C36, C37, C38, C39, C40, C41, C42, C43, C44, C45, C46, C47, C48, C49, C51, C52, C55, C58, C59, C61, C62, C63, C64, C66, C67, C68, C69, C70, C71, C74 C75, C77, C78, C80, C81, C82, C83, C84, C85, C86, C100, C101, C102, C103, C104, C105, C106, C107, C108, C109, C110, C111, C113, C114, C115, C116, C117, C118, C119, C120, C121, C122, C123, C124, C125, C126, C127, C128, C129, C131, R4, R5, R10, R12, R14, R15, R16, R17, R19, R24, R21, R22, R23, R24, R25, R26, R34, R38	0402	Cap, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2, Res2	120
	Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Capacitor, Resistor	C7, C22, C30, C50, C53, C54, C56, C57, C60, C65, C72, C73, C76, C79, C99, C112, C130, C131, R1, R2, R3, R6, R7, R8, R9, R11, R13, R18, R27, R28, R29, R30, R31, R32, R33, R35, R36, R37, R39	0603	Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Cap, Res2	39
LED0	Typical INFRARED GaAs LED	D1	LED-0	LED0	1
LED1	Typical INFRARED GaAs LED	D2	LED-0	LED0	1
LED2	Typical INFRARED GaAs LED	D3	LED-0	LED0	1
LED3	Typical INFRARED GaAs LED	D4	LED-0	LED0	1
LED4	Typical INFRARED GaAs LED	D5	LED-0	LED0	1
Component_1		J9, J10	CONN84-1_0- 717420001	Component_1	2
BLM18EG2215N1D	Resistor	L1, L2, L7, L8, L9, L10, L11, L12, L13, L14, L15, L16, L17, L18, L19, L20, L21, L22, L23, L24, L25	0603	Res2	21
	Resistor	L3, L4, L5, L6	0805	Res2	4
ADP151AUJZ-3.3-R7		U1	TSOT	Component_1	1
BT0507		U2	SMD4-	Component_1	1
LMK00105		U3	QFN24-050-0404LH	Component_1	1
FIN1001		U4	SOT23-5	Component_1	1
HSMS-282R		U5	SOT-363	Component_1	1
NCS2-592+		U6, U10	FLT6-26-0212	Component_1	2
AD9361		U7	BGA144-32-1212	Component_1	1
NCS1-63+		U8, U9	FLT6-26-0212	Component_1	2
ADM7172ACPZ-5.0-		U11	DFN8-050-0303LH	Component_1	1
ADP3339AKC-3.3-RL		U12	SOT-223	Component_1	1
ADP3339AKC-2.5-RL		U13	SOT-223	Component_1	1
ADP1755		U14, U15	QFN16-065-0404LH	Component_1	1