

Thermal Metric	MAX3232D	MAX3232PW	MAX3232DB	MAX3232DW	Unit
T_A	25C				
$R_{\theta JA}$	78.1	101.1	93.5	66.6	°C/W
$R_{\theta J Ctop}$	38.5	32.9	45.8	32.4	
$R_{\theta JB}$	36.3	47.5	44.6	31.9	
Ψ_{JT}	8	1.9	11.1	8.4	
Ψ_{JB}	36	46.9	44	31.5	