

Serial Number:000001

24C9N5K 8只 (亿德发提供)				
Chan	SNR_Dt	Zero(mV)	INL(thou)	DIV
0	88254	46.38	0.19	0.991
1	85737	46.64	0.16	1.009
2	86763	47.15	0.15	1.009
3	83422	46.7	0.19	0.997
4	67473	46.06	0.18	0.997
5	37314	46.63	0.17	1.016
6	49006	46.54	0.2	0.998
7	49885	46.13	0.23	0.994
8	96139	45.01	0.17	1
9	93567	45.31	0.17	1.006
10	94210	45.51	0.16	1
11	97841	45.44	0.16	0.995
12	94159	45.41	0.15	1.001
13	80954	45.29	0.17	1.003
14	94612	45.39	0.18	1.003
15	98458	45.16	0.21	0.996
16	78879	45.78	0.16	1.006
17	82373	45.85	0.16	0.988
18	84230	46.18	0.16	0.992
19	81525	45.92	0.16	1.006
20	83845	45.39	0.14	0.996
21	81362	45.91	0.14	1.021
22	81882	45.72	0.14	0.987
23	81174	46.12	0.16	1.007
24	95046	45.59	0.14	0.995
25	91886	45.06	0.13	0.997
26	92039	45.41	0.1	1.014
27	93601	45.26	0.15	0.99
28	92775	46.21	0.12	0.995
29	92626	45.57	0.14	1.011
30	93269	45.63	0.14	0.989
31	95589	45.68	0.19	0.994

OAA17RK 8只 (工装子板)			
SNR_Dt	Zero(mV)	INL(tho)	DIV
90138	46.39	0.19	1.004
86553	46.6	0.15	1.008
86695	47.15	0.15	1.013
89389	46.73	0.19	0.991
88758	46.07	0.18	0.987
87881	46.65	0.17	1.02
88323	46.51	0.2	0.996
88700	46.17	0.23	0.994
97849	45.02	0.17	0.999
93125	45.31	0.17	1.006
94096	45.51	0.16	1
95764	45.45	0.15	0.995
99080	45.42	0.14	1.001
109866	45.31	0.16	1.003
92641	45.4	0.18	1.003
97271	45.18	0.2	0.996
81599	45.78	0.16	0.993
82528	45.86	0.16	0.989
83503	46.19	0.15	0.988
81939	45.92	0.15	1.009
82734	45.39	0.14	1.006
83713	45.9	0.13	1.017
83613	45.72	0.13	0.989
81323	46.11	0.16	1.007
94587	45.59	0.14	0.996
96483	45.07	0.13	0.997
90201	45.41	0.1	1.014
95668	45.27	0.15	0.99
91640	46.21	0.12	0.995
93573	45.57	0.14	1.011
93427	45.62	0.14	0.989
91095	45.68	0.18	0.995

