

Serial Number:000001

24C9N5K 8只 (亿德发提供)				
Chanr	SNR_Dt	Zero(mV)	INL(tho)	DIV
0	138523	46.39	0.19	1.02
1	135968	46.64	0.16	1.02
2	138580	47.12	0.16	1.02
3	140646	46.72	0.17	1.02
4	106793	46.11	0.16	1.02
5	61558	46.72	0.17	1.03
6	77166	46.5	0.18	1.03
7	71105	46.09	0.22	1.01
8	142643	45.34	0.17	0.99
9	141221	45.75	0.15	1
10	137635	45.68	0.15	0.99
11	148486	45.23	0.18	0.98
12	148967	44.9	0.15	1.02
13	144005	45.41	0.16	1.01
14	152444	45.29	0.17	0.98
15	148715	44.74	0.19	0.98
16	130173	46.42	0.14	1
17	124670	45.9	0.14	1.02
18	131521	45.93	0.12	1.01
19	130316	45.74	0.15	0.97
20	131982	45.96	0.13	0.98
21	130914	45.97	0.1	1.01
22	124242	45.98	0.14	1.04
23	118809	45.8	0.16	1.02
24	145920	44.97	0.16	0.96
25	140892	44.82	0.15	0.98
26	139570	45.2	0.12	0.97
27	138049	45.19	0.16	0.97
28	130161	45.85	0.14	1.01
29	138961	45.26	0.16	0.99
30	143705	45.86	0.16	0.96
31	148352	45.56	0.2	1

OAA17RK 8只 (工装子板)			
SNR_Dt	Zero(mV)	INL(tho)	DIV
142665	46.34	0.19	1.015
142296	46.59	0.15	1.022
137667	47.07	0.15	1.016
143168	46.67	0.17	1.023
137545	46.09	0.16	1.018
138338	46.73	0.16	1.033
132498	46.49	0.17	1.03
140852	46.11	0.21	1.011
138956	45.34	0.16	0.993
136417	45.73	0.15	0.997
141581	45.68	0.15	0.987
143138	45.23	0.18	0.977
149153	44.93	0.15	1.02
140727	45.44	0.16	1.014
146900	45.31	0.17	0.98
142645	44.77	0.19	0.983
130938	46.41	0.14	1.003
125285	45.89	0.14	1.021
128083	45.91	0.11	1.011
136322	45.73	0.15	0.966
135074	45.94	0.13	0.982
128430	45.94	0.1	1.005
123714	45.96	0.14	1.037
127250	45.77	0.16	1.021
149066	44.96	0.15	0.96
141506	44.81	0.14	0.979
133681	45.19	0.12	0.969
138833	45.19	0.16	0.973
129303	45.84	0.14	1.007
140359	45.24	0.16	0.993
145154	45.84	0.16	0.955
145163	45.55	0.19	1.001

