



Selection

- ◇ RP+L
- ◇ LHR
- ◆ **Apps Calculator**
- ◇ Register Configurat
- ◇ About

COM Port  COM11 


 Save Config

 Load C

NO TARGET (d=inf)

MAX TARGET (d=0)

Sensor Parameters :			Sensor Parameters :		
Csensor	15pF	Too Small	Lvariation	0.7	
Lsensor (No Targ)	24uH		Lsensor (Final)	16.80uH	
Fsensor (No Targ)	8.39MHz		Fosc (Final)	10.03MHz	Too Large
Rs_parasitic	1.50hms		Rpvariation	0.7	
Rp_parasitic	1.07MOhms		Rp_parasitic	522.67kOhms	
Loop Parameters :			Loop Parameters :		
Rp_Min	3k (Ohms) 	Too Small	Rp_Min	3k (Ohms) 	Too Small
Rp_Max	24k (Ohms) 	Too Small	Rp_Max	24k (Ohms) 	Too Small
Qmin	843.27	Too Large	Qmin	2.83	Too Small
C1 (No Target)	3p (F) 		C2 (Final)	3p (F) 	
R1 (No Target)	29.81kOhms	Too Small	R2 (Final)	24.94k (Ohms)	Too Small
C2 (No Target)	12p (F) 		C1 (Final)	12p (F) 	
R2 (No Target)	7.50k (Ohms)		R1 (Final)	7.50k (Ohms)	

 Update Registers