

OneUI Application

MENU

Sensing Solutions EVM GUI

v1.8.8

Current Drive and Power

Power Mode

☒ Enable Low Power Sensor Activation Mode (Recommended)

☐ Enable High Current Sensor Drive (ch0 only)

Sensor Initialization Current

| Channel | I _{drive} | | Detect I _{drive} Init | |
|---------|--------------------|--------------|--------------------------------|--------------|
| | Code | Current (uA) | Code | Current (uA) |
| 0 | 17 | 196 | 14 | 126 |
| 1 | 17 | 196 | 14 | 126 |
| 2 | 17 | 196 | 0 | 16 |
| 3 | 17 | 196 | 0 | 16 |

Device Status

Error Channel: 1

Conversion Under-range Error

Conversion Over-range Error

Watchdog Timeout Error

Amplitude High Warning

Amplitude Low Warning

Zero Count Error

Data Ready Flag

Channel 0 Unread Conversion

Channel 1 Unread Conversion

Channel 2 Unread Conversion

Channel 3 Unread Conversion

Connected

Data streaming stopped

TEXAS INSTRUMENTS

Is this error of GUI?