






DISPLAY MODE	HTN/POSITIVE/REFLECTIVE	DUTY 1/4	BITS 1/3	4	PIN TABLE	YY101203	ADKOM™	Elektronik GmbH , Germany
VIEWING ANGLE	6:00 0° CLOCK	SAMPLE	1/4	3	DRAWING	YY101021		
DRIVING VOLTAGE	3.0 V	APPLICATION:		2	shift icons	YY101020	MODEL NO	FH-1152P
OPERATING TEMP	-10° C TO 60° C	INSTRUMENT		1	SIZE\NAME	YY101019	CUSTOMER NO	
STORAGE TEMP	-20° C TO 70° C	AIR-CONDITION			MODIFY CONTENTS	YY101018	CUSTOMER	
CONNECTOR	PIN	OTHER			CROSSING POINTS IN THE LINE		TOLERANCES UNLESS OTHERWISE STATED	X: ±0.2 X: ±0.10 ANGLE ±5°



PIN	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44
COM0	RX	A6P				COM0	BATT		D4D	D4DP	D3D	D3DP	D2D	D2DP	D1D	DCOL	DNEG	U	PN	PNE	) 2	TMR2
COM1	A6N	A6K			COM1		B2	B1	D4C	D4G	D3C	D3G	D2C	D2G	D1C	D1G	REC	R	PE	PSE	) 1	TMR1
COM2	TX	A6J		COM2			B4	B3	D4B	D4F	D3B	D3F	D2B	D2F	D1B	D1F	PM	D	PS	PSW	(2	HRT
COM3	A6Q	A6H	COM3				B6	B5	D4A	D4E	D3A	D3E	D2A	D2E	D1A	D1E	ALM	L	PW	PNW	(1	i

	ADKOM TM Elektronik GmbH , Germany			
MODEL NO	FH-1152P	DWN:	YY20100908	UNIT mm
CUSTOMER NO		CHK:	GRH20100908	SCALE 1 : 1
CUSTOMER		APP:		SHEET SHEET 2 OF 2
TOLERANCES UNLESS OTHERWISE STATED X:±0.2 XY:±0.10 ANGLE±5°				