

cf.json

C: > ti > mmwave_studio_02_01_01_00 > mmWaveStudio > PostProc > cf.json > ...

```
1 [
2 "DCA1000Config": {
3   "dataLoggingMode": "raw",
4   "dataTransferMode": "LVDSCapture",
5   "dataCaptureMode": "ethernetStream",
6   "lvdsMode": 2,
7   "dataFormatMode": 3,
8   "packetDelay_us": 25,
9   "ethernetConfig": {
10    "DCA1000IPAddress": "192.168.33.180",
11    "DCA1000ConfigPort": 4096,
12    "DCA1000DataPort": 4098
13  },
14  "ethernetConfigUpdate": {
15    "systemIPAddress": "192.168.33.30",
16    "DCA1000IPAddress": "192.168.33.180",
17    "DCA1000MACAddress": "12.34.56.78.90.12",
18    "DCA1000ConfigPort": 4096,
19    "DCA1000DataPort": 4098
20  },
21  "captureConfig": {
22    "fileBasePath": "D:\\git\\ar1xxx_mmwavestudio_bitbucket\\mmWaveStudioPkg\\mmWaveStudio_Internal\\PostProc",
23    "filePrefix": "lua_check",
24    "maxRecFileSize_MB": 1024,
25    "sequenceNumberEnable": 1,
26    "captureStopMode": "infinite",
27    "bytesToCapture": 4000,
28    "durationToCapture_ms": 4000,
29    "framesToCapture": 40
30  },
31  "dataFormatConfig": {
32    "MSBToggle": 0,
33    "laneFmtMap": 0,
34    "reorderEnable": 0,
```

窗口视图(W)