



VDDA_1V8_PHYA	◇	VDDA_1V8_PHYA	4,10
VUSB_3V3	◇	VUSB_3V3	4
VDD_3V3	◇	VDD_3V3	2,3,4,6,7,8,9,10,11,12,13,15,16,17,18,24,25,26,27