



<50>PDO_1 >> PDO_1
 <50>PDO_2 >> PDO_2
 <50>PDO_3 >> PDO_3

PDO_3	PDO_2	PDO_1	Output Voltage	Feedback (R1)	Feedback (R2)	Output Voltage
0	0	0	5V	30k	9.53k	5.14V
0	0	1	9V	30k	4.59k	9.33V
0	1	0	15V	30k	2.64k	15.32
1	0	0	20V	30k	1.79k	22.03



