



Signal description (measuring point)

Ch1 : +1.1VD_U1	Power supply input to VDD11 pin of TUSB7320. (Measure the Voltage value)
CH2 : +3.3VD	Power supply input to VDD33 pin of TUSB7320. (Measure the Voltage value)
CH3 : XHCI1_48M_CLK	Signal input to the XI pin of the TUSB7320. (Measure the Voltage value)
CH4 : XHCI1_GRST_X	Signal input to the GRST pin of the TUSB7320. (Measure the Voltage value)