

RefDes	Value	Name
C7	0,1 мк	CC8885KRX7R96B104
C8	10 мк, 25 В	CB825M0010R5B-8485
C9	0,1 мк	CC8885KRX7R96B104
C10	0,01 мк	CC8885KRX7R7BB103
C11	0,1 мк	CC8885KRX7R96B104
C12	0,1 мк	CC8885KRX7R96B104
C13	10 мк, 25 В	CB825M0010R5B-8485
C14	0,1 мк	CC8885KRX7R96B104
C15	0,1 мк	CC8885KRX7R96B104
C16	10 мк	GRM31MF51A106ZA01L
C17	0,1 мк	CC8885KRX7R96B104
C20	0,1 мк	CC8885KRX7R96B104
C23	10 мк	GRM31MF51A106ZA01L
C26	0,01 мк	CC8885KRX7R7BB103
C27	0,1 мк	CC8885KRX7R96B104
C28	0,047 мк	GRM21BR71H473KA01L
DD1	Микроконтроллер	STM32F303CCT6
DD2	ADM3053BRWZ	ADM3053BRWZ
FV2	24 В	NUP210SLT9G
R12	10 к	RC8885JR-0718KL
R14	0	RC8885JR-078RL
R16	30	CRCW888538R0JNEAHP
R17	30	CRCW888538R0JNEAHP
XP2	"SWD"	B08-PH-K-S
XP4.1	"Выход"	B18B-PH-K-S
Z2	1,8 кОм	BLM21BD182SN1D
Z3	1,8 кОм	BLM21BD182SN1D
Z4	1,8 кОм	BLM21BD182SN1D

