




LAN_P2




Pin Name	Strap mode	PU Resistor	PD Resistor
COL CRS RX_ER	1	OPEN	1.96K
	2	13K	1.96K
	3	6.2K	1.96K
	4	OPEN	OPEN
RX_D0 RX_D1 RX_D2 RX_D3 RX_DV	1	OPEN	OPEN
	2	10K	2.49K
	3	5.76K	2.49K
	4	2.49K	OPEN

```
Set PHY Address to 6:
COL:Mode2
RX_D0:Mode4
RX_D1:Mode4
RX_D2:Mode1
RX_D3:Mode1
```



DC/DC



LAN_P2-Fiber1

OPTION5 Optical Fiber

