


IPC Debug

PWA data

Bd No.	PWA S/N	DP83865DVH	3V3	2V5A	1V8A	Auto Neg	PHY address
#1	HL02E1BA	64AXE3UG3	3.312	2.546	1.818	ON	0x1, open pin
#2	HL02E1B8	64AXE4UG3	3.332	2.549	1.825	OFF 100M fix	0x1, open pin
#3	HL02E1BB	64AXE4UG3	3.326	2.552	1.810	ON	0x1, resister strap
#4	HL02E1B9	64AXE4UG3	3.320	2.537	1.817	ON	0x1, resister strap
#5	HL02E1B7	64AXE4UG3	3.308	2.534	1.810	ON	0x1, resister strap


IPC Debug

Power on




IPC Debug

PHY CLK_IN 25MHz



IPC Debug

MDIO/MDC



rd 0x01008200
PHY address=1

IPC Debug

MDIO/MDC-inverted clock



rd 0x01008200
PHY address=1



wr 0x01008200 0x9300
PHY address=1