


V+

0.047µF C1 and 0.047µF C2


Added 3kΩ load during measurement




V-

0.047µF C1 and 0.047µF C2

Added 3kΩ load during measurement



H



V+

0.047µF C1 and 0.047µF C2

Added 3kΩ load during measurement

Different timing