

2018-07-10
11:36:02



Diagram1: Ch1,Ch2

光标结果 1

-17.6 μ s V1 2.30253 V
-1.6 μ s V2 2.6006 V
16 μ s Δ V 298.07 mV
62.5 kHz Δ V/ Δ t 18.629 kV*Hz

跟踪波形

水平

Res: 400 ns / 2.5 MSa/s

RL: 1 kSa

RT

Scl: 40 μ s/div

Pos: 66.4 μ s

触发

Normal

A: Edge Ch2

Lvl: 2.69598 V

Ch1Wfm1

Scl: 500 mV/div

Pos: -4 div

Off: 0 V

Cpl: DC 1M Ω

Dec: Sa TA: Off

BW: 500 MHz

Ch2Wfm1

Scl: 500 mV/div

Pos: -4 div

Off: 0 V

Cpl: DC 1M Ω

Dec: Sa TA: Off

BW: 20 MHz

TA

