


Lab Notebook Entry from LeCroy DSO
DSO S/N: LCRY0614N49164
User: LeCroyUser
Time: 12/10/2014 2:49:48 PM

12/10/2014 2:49:48 PM

Power Supplies
Yellow - 3.3V
Red - 1.8V



Channel Status

	C1	C2
Vertical	V / Div	50.0 mV
	Offset	-3.3000 V
	Coupling	DC1M Ω
	BW-Limit	Full
	Probe	10
	Sweeps	1 #

Acquisition Status

Horizontal	Time / Div	20.0 ns	Sampling Rate	5.0 GS/s
	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	100.0 S	Trigger Delay	-80.0000 μ s
Trigger	Mode	Stop	Slope	Positive
	Type	Edge	Level	1.6950 V
	Source	C2	Coupling	DC

