



Table

	仕様1	仕様2
OPA313		
Cin+ / Cin-	0.22uF	0.022uF
Rin+ / Rin-	3.6k	36k
Cout+ / Cout-	2200pF	220pF
Rout1+ / Rout1-	10k	100k
Rout2+ / Rout2-	13k	130k
GAIN	+3.5dB	+3.9dB
HPF	191Hz	200Hz
LPF	12.8kHz	12.8kHz

マルツエレクトロニクス株式会社  
 Title Mic amp for Panasonic [OPA313]  
 Size A Document Number Rev 1.0  
 Date: Feb. 22, 2022 Sheet 1 of 1

Rev	Date	改版内容
v1.0	2022/02/22	OPA313バージョン