

Channels	48 Bi-directional (24 for USB-4751L)	
Programming Mode	8255 PPI Mode0	
Input Voltage	Low	0.8 V max
	High	2.0 V min
Output Voltage	Low	0.5 V max. @ 12mA (sink)
	High	3.8 V min. @ -12mA (source)(each line) 3.8 V min.@5mA(source)(high of every line)
+5V Output	100mA max.	
Interrupt Mode	PC0 source; PC4 gate/PC0 source	

A 2 Counter