


```

*    SURFACE - AIR 0 MM
L1 TOP CONDUCTOR - COPPER 0.035 MM
*    DIELECTRIC - 2116PV170 0.122 MM
*    DIELECTRIC - 106PV170 0.048 MM
L2 L2 PLANE - COPPER 0.017 MM
*    DIELECTRIC - FR-4 1.14 MM

L3 L3 PLANE - COPPER 0.017 MM
*    DIELECTRIC - 2116PV170 0.122 MM
*    DIELECTRIC - 106PV170 0.048 MM
L4 BOTTOM CONDUCTOR - COPPER 0.035 MM
*    SURFACE - AIR 0 MM

```

TOTAL THICKNESS 1.59 MM +/- 0.16 MM after press



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	FINISHED_SIZE	PLATED	QTY
⊙	0.2	PLATED	289
⊙	0.2	PLATED	25
△	1.501	NON-PLATED	4