






Test Setting:( CC1120DK\_EM\_868\_915) Rev1.1.0







- |                |          |
|----------------|----------|
| ▪ RMS/Ave      | -57.4dBm |
| ▪ Pos/Ave      | -52.0dBm |
| ▪ Pos/Max hold | -46.6dBm |
| ▪ RMS/Max hold | -54.1dBm |