



17/12/2024 14:31:50

| Channel | Name | Span | Value | Min. | Max. | \bar{x} | σ |
|---------|-----------|-------------|-----------|-----------|-----------|-----------|-----------|
| A | Frequency | Whole trace | 4.923 MHz | 654.4 kHz | 5.814 MHz | 2.584 MHz | 2.005 MHz |
