

2016-02-11 15:22:07.5643: Log Panel Cleared  
 2016-02-11 15:22:13.9042: Message Sent:  
     0x01 80 04 00 2A 81 00 00  
 2016-02-11 15:22:13.9042: Sending: (0x01) - SystemInformation.Request:  
 2016-02-11 15:22:13.9242: Message Received:  
     0x01 00 3E 00 2E 50 00 00 04 07      0x07 07 06 00 36 37 38 39 30 31  
     0x32 33 34 35 36 37 38 39 43 F8      0x03 04 00 00 36 37 16 21 DC 01  
     0x00 00 00 00 00 00 00 00 00 00      0x00 00 00 00 00 00 00 00 FF 01  
     0x55 74 00 00 00 00  
 2016-02-11 15:22:13.9242: Receiving: (0x01) - SystemInformation:  
     Firmware Version: Major:7 Minor:7 Revision:7 Build:4  
     Device Type: G3  
     Device Mode: Lower MAC Mode  
     Hardware Revision: 0  
     Diagnostics Port: SCI A  
     Data Port: SCI A  
     Coherent Modulation: Off  
     Tonemask Req Mode: Non Designated  
     Long Address 0x00 00 00 00 00 00 FF 01  
 2016-02-11 15:22:13.9442: Message Sent:  
     0x0C 80 22 00 EC 14 4E C3 03 00      0x1A 00 00 00 00 00 00 00 00 00  
     0x00 00 00 00 00 00 00 00 00 00      0x00 00 00 00 00 00 04 00  
 2016-02-11 15:22:13.9442: Sending: (0x0C) - Load System Config.Request  
     Load System Configuration.Request  
     Configuration Type: System Configuration  
     Length: 26  
     Device Mode: Lower MAC Mode  
 2016-02-11 15:22:13.9542: Message Received:  
     0x0C 00 06 00 94 E5 00 00 00 00  
 2016-02-11 15:22:13.9542: Receiving: (0x0C) - LoadSystem Config.StatusReply: Status= Success - 0x0000  
 2016-02-11 15:22:13.9542: Message Sent:  
     0x0C 80 18 00 B2 FE E4 63 08 00      0x10 00 00 00 00 00 00 00 00 00  
     0xFF 01 00 00 00 00 EF 00  
 2016-02-11 15:22:13.9542: Sending: (0x0C) - Load System Config.Request  
     Load G3 Configuration.Request  
     Configuration Type: G3 Configuration  
     Length: 16  
     Coherent Modulation: Off  
     Tonemask Req Mode: Non Designated  
     G3 Long Address: 0x00 00 00 00 00 00 FF 01  
 2016-02-11 15:22:13.9742: Message Received:  
     0x0C 00 06 00 94 E5 00 00 00 00  
 2016-02-11 15:22:13.9742: Receiving: (0x0C) - LoadSystem Config.StatusReply: Status= Success - 0x0000  
 2016-02-11 15:22:13.9742: Message Sent:  
     0x14 C0 06 00 07 5D 62 66 02 00  
 2016-02-11 15:22:13.9742: Sending: (0x14) - Get Info.Request: TLV Id= G3 PHY TX  
 2016-02-11 15:22:13.9942: Message Received:  
     0x14 00 1C 00 48 97 00 00 00 00      0x02 00 12 00 00 03 0C 00 17 24  
     0xFF FF FF FF 0F 00 00 00 00 00      0x00 00  
 2016-02-11 15:22:13.9942: Receiving: (0x14) - Get Information: Response:  
     Status: Success  
     Type: G3 PHY TX  
     Length: 18  
     TMR: Non Designated  
     FCC Europe Mode: Off  
     COH: Off  
     Band Selection: CENELEC  
     Modulation: 8PSK  
     TX Level: 12  
     Tone Mask:0x17 24 FF FF FF FF 0F 00 00 00 00 00 00 00  
 2016-02-11 15:22:13.9942: Message Sent:  
     0x0D 80 0E 00 D3 21 C2 27 0F 01      0x00 01 00 00 02 00 55 74  
 2016-02-11 15:22:13.9942: Sending: (0x0D) - Set G3 MAC PIB.Request:  
     PIB: PAN Id - 0x0100010F:  
         Len= 2  
         Index= 0  
         Value=0x7455  
 2016-02-11 15:22:14.0042: Message Received:  
     0x0D 00 06 00 20 93 00 00 00 00  
 2016-02-11 15:22:14.0042: Receiving: (0x0D) - Set MAC PIB.StatusReply: Status= Success - 0x0000

2016-02-11 15:22:14.0142: Message Sent:  
0x00 80 47 00 01 AF D9 17 01 08 0x00 0C FF FF 03 0B 00 FF FF FF  
0xFF FF FF 00 00 14 00 01 04 14 0x21 DC 01 55 74 00 00 00 00 00  
0x00 FF 02 55 74 00 00 00 00 00 0x00 FF 01 30 31 32 33 34 35 36  
0x37 38 39 30 31 32 33 34 35 36 0x37 38 39 43 F8

2016-02-11 15:22:14.0142: Sending: (0x00) - G3 DC DataTransfer.Request V1  
Interface: Primary  
NSDU Handle: 1  
ARQ: Enabled  
QoS: Standard Priority  
Band Selection: CENELEC  
Protocol: G3  
Power Level: 12  
Tone Map: 0xFF FF 03  
Resolution: 6 dB  
Gain: 1  
Modulation: 8PSK  
TX Coef: 0xFF FF FF FF FF FF  
COH: Off  
MPDU Payload Length: 20  
MPDU:  
0x01 04 14 21 DC 01 55 74 00 00 0x00 00 00 00 FF 02 55 74 00 00  
0x00 00 00 00 FF 01 30 31 32 33 0x34 35 36 37 38 39 30 31 32 33  
0x34 35 36 37 38 39 43 F8

2016-02-11 15:22:14.0842: Message Received:  
0x00 10 08 00 CA CA 00 00 01 80 0x00 00

2016-02-11 15:22:14.0842: Receiving: (0x00) - G3 DataTransfer.Confirmation: - Status= 0000  
NSDU Handler: 1  
Confirm Flag: Confirm  
Status: 0x0000

2016-02-11 15:22:14.1342: Message Received:  
0x00 00 50 00 BF 0E 00 00 88 78 0x00 C3 3F 16 A6 00 00 00 00 00  
0x6C 3F 00 00 03 88 00 00 00 00 0x00 00 00 00 14 00 01 00 14 21  
0xDC 01 55 74 00 00 00 00 00 00 0xFF 01 55 74 00 00 00 00 00 00  
0xFF 02 30 31 32 33 34 35 36 37 0x38 39 30 31 32 33 34 35 36 37  
0x38 39 32 D4

2016-02-11 15:22:14.1342: Receiving: (0x00) - G3 DC DataTransfer.Indication V3  
Interface: Primary  
LQI: 53.0 dB  
Confirmation: Indication  
RX\_Phase: 15  
FCH: 0x0x00 C3 3F 16 A6 00 00 00 00  
Band Selection: CENELEC  
Protocol: G3  
Power Level: 108  
Tone Map: 0x3F 00 00  
Resolution: 6 dB  
Gain: 0  
Modulation: 8PSK  
LQI: 53.0 dB  
TX Coef: 0x00 00 00 00 00 00  
MPDU Payload Length: 20  
MPDU:  
0x01 00 14 21 DC 01 55 74 00 00 0x00 00 00 00 FF 01 55 74 00 00  
0x00 00 00 00 FF 02 30 31 32 33 0x34 35 36 37 38 39 30 31 32 33  
0x34 35 36 37 38 39 32 D4