











## I2C Address

| DESCRIPTION      | BINARY DEVICE ADDRESS |   |   |   |   |   |   |     | ADDRESS PINS |      |      |      |
|------------------|-----------------------|---|---|---|---|---|---|-----|--------------|------|------|------|
|                  | 6                     | 5 | 4 | 3 | 2 | 1 | 0 | A4  | A3           | A2   | A1   |      |
| Broadcast access | 1                     | 1 | 1 | 1 | 1 | 1 | 1 | 0   | X            | X    | X    | X    |
| Slave 0          | 0                     | 1 | 0 | 0 | 0 | 0 | 0 | 0/1 | GND          | GND  | GND  | GND  |
|                  | 0                     | 1 | 0 | 0 | 0 | 1 | 0 | 0/1 | GND          | GND  | GND  | HIGH |
|                  | 0                     | 1 | 0 | 0 | 1 | 0 | 0 | 0/1 | GND          | GND  | HIGH | GND  |
|                  | 0                     | 1 | 0 | 0 | 1 | 1 | 0 | 0/1 | GND          | GND  | HIGH | HIGH |
|                  | 0                     | 1 | 0 | 1 | 0 | 0 | 0 | 0/1 | GND          | HIGH | GND  | GND  |
|                  | 0                     | 1 | 0 | 1 | 0 | 1 | 0 | 0/1 | GND          | HIGH | GND  | HIGH |
|                  | 0                     | 1 | 0 | 1 | 1 | 0 | 0 | 0/1 | GND          | HIGH | HIGH | GND  |
|                  | 0                     | 1 | 0 | 1 | 1 | 1 | 0 | 0/1 | GND          | HIGH | HIGH | HIGH |
|                  | 0                     | 1 | 1 | 0 | 0 | 0 | 0 | 0/1 | HIGH         | GND  | GND  | GND  |
|                  | 0                     | 1 | 1 | 0 | 0 | 1 | 0 | 0/1 | HIGH         | GND  | GND  | HIGH |
|                  | 0                     | 1 | 1 | 0 | 1 | 0 | 0 | 0/1 | HIGH         | GND  | HIGH | GND  |
|                  | 0                     | 1 | 1 | 0 | 1 | 1 | 0 | 0/1 | HIGH         | GND  | HIGH | GND  |
|                  | 0                     | 1 | 1 | 1 | 0 | 0 | 0 | 0/1 | HIGH         | HIGH | GND  | GND  |
|                  | 0                     | 1 | 1 | 1 | 0 | 1 | 0 | 0/1 | HIGH         | HIGH | GND  | HIGH |
|                  | 0                     | 1 | 1 | 1 | 1 | 0 | 1 | 0/1 | HIGH         | HIGH | HIGH | GND  |
| Slave 15         | 0                     | 1 | 1 | 1 | 1 | 1 | 0 | 0/1 | HIGH         | HIGH | HIGH | HIGH |
|                  | 0                     | 1 | 1 | 1 | 1 | 1 | 1 | 0/1 | HIGH         | HIGH | HIGH | HIGH |


## POE Manager Slave (90W)#2




### POE Manager Slave (90W)#3




# POE Manager Slave (90W)#4




# POE Manager Slave (30W)#1



## POE Manager Slave (30W)#2



# POE Manager Slave (30W)#3



# POE Manager Slave (30W)#4

