



Cursors Measure

Search Results Table

Draw Zoom More ...

Meas 1 **3**
Max
392.1 mA

Ch 1
5.00 V/div
20 MHz BW

Ch 2
2.00 V/div
20 MHz BW

Ch 3
100 mA/div
1 M Ω
20 MHz BW

4 Math Ref Bus DVM

Horizontal
4.00 ms/div
SR: 25.0 MS/s
RL: 1 Mpts

Trigger **3**
48.0 mA

Acquisition
High Res
Single: 1/1

RF

Preview
30 Jan 2025
20:08:15