



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	100.9 kHz	21.544 kHz	-79.356 kHz
Trace 1	Magnitude (dB)	Magnitude (dB)	Magnitude (dB)
Measurement	41.134 dB	47.517 dB	6.383 dB

Sweep	
Start frequency:	1 kHz
Stop frequency:	10 MHz
Center frequency:	5 MHz
Span:	9.999 MHz
Sweep mode:	Logarithmic
Numer of points:	201

Calibration	Full-Range	User-Range
Gain	Active	-

Termination	Channel 1	Channel 2
Gain	1 MΩ	1 MΩ

Attenuator setting	Channel 1	Channel 2
Transmission	0 dB	0 dB

Hardware setup	
Device type:	Bode100R2
Serial number:	PC200H
Receiver bandwidth:	30 Hz
Output level:	100 mVpp
DUT settling time:	10 ms