

Flat Pack Specification Sheet

CONTROLING DOCUMENT

PACKAGE TYPE:

FOOT CONFIGURATION:







FA / FS NUMBER

CUSTOMER Texas Instruments

PART NUMBER 16HKR Krypton

DATE 11/18/2014

DRAWN BY TL



DIMENSIONS	TOLERANCE
A	0.00 ±0.002
C	0.006 ±0.002
D	0.58 ±0.02
E	0.05 ±0.005
X	0.--- ±0.---
F	0.100 ±0.020
G	0.012 ±0.002
H	0.012 ±0.002
J	0.030 ±0.005
M	0.38 ±0.010
N	0.26 ±0.010
PACKAGE LENGTH	Y 0.435 ±0.015
LEAD WIDTH	L 0.020 ±0.005
PITCH	0.05
# OF LEADS PER SIDE	8

LEADS TINNED:

YES NO

CONTROLLING UNITS:

METRIC INCHES

PACKAGE TYPE

METAL CERAMIC
 PLASTIC GLASS SEAL

LEAD TYPE:

FLAT ROUND
 UP 0-4° DOWN 0-4°

APPROVED Tomaso R. S.C. DATE 11/19/2014

BY Jessica M. Haggarty

Template Version 3/3/14