

Cursors Callout

Measure Search


Results Table Plot

More...

Meas 1
Maximum
µ: 2.942 A

Meas 2
Minimum
µ: -3.125 A

Meas 3
Frequency
µ: 94.36 kHz



Double tap to edit

Double tap to edit

Ch 2
1 A/div
1 MΩ
20 MHz B_w

1 3 4
Add New Math
Add New Ref
Add New Bus

Horizontal
100 µs/div 1 ms
SR: 1.25 GS/s 800 ps/pt
RL: 1.25 Mpts 50%

Trigger
2.92 A

Acquisition
Auto, Analyze
Sample: 12 bits
Single: 1/1

Stopped
25 Feb 2022
12:10:21 AM