



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION. GOOD SEED CDC RESERVES ALL RIGHTS TO THIS DRAWING, INCLUDING PATENT APPLICATION RIGHTS. TRANSMITTAL TO THIRD PARTIES, REPRODUCTIONS, OR ANY OTHER FORM OF DISTRIBUTION IS FORBIDDEN WITHOUT THE PRIOR WRITTEN CONSENT OF GOOD SEED CDC OR ITS REPRESENTATIVES.

<b>Title: AC/DC Power Supply</b>		
Document Name: Flyback_Power_Supply.SchDoc	Revision: *	
Size: A3	Drawn By: K.E	Sheet * of *

Designator	Description	Quantity	Supplier Part Number 1	Manufacturer Part Number
C1	CAP CER 0.1UF 630V X7R 1812	1	478-4009-1-ND	1812CC104KAT1A
C2	CAP ALUM 15UF 20% 400V RADIAL	1	EEU-ED2G150B	EEU-ED2G150B
C3	CAP ALUM 47UF 20% 400V RADIAL	1	P13546-ND	EEU-ED2G470S
C4, C6, C7	CAP ALUM POLY 470UF 20% 6.3V T/H	3	493-4019-1-ND	RL80J471MDNASQKX
C5, C12	CAP CER 1UF 10V X7S 0402	2	490-13409-1-ND	GCM155C71A105KE38D
C8	CAP FILM 0.22UF 20% 630VDC RAD	1	495-4371-3-ND	B32922C3224M289
C9	CAP CER 0.022UF 50V X7R 0402	1	490-3884-1-ND	GRM155R71H223KA12D
C10	CAP CER 4.7UF 25V X7R 0805	1	445-173713-1-ND	CGA4J1X7R1E475M125AE
C11	CAP CER 4700PF 440VAC Y5U RADIAL	1	BC2359-ND	VY2472M49Y5US63V7
C13	CAP CER 10000PF 50V X7R 0402	1	490-4516-1-ND	GRM155R71H103KA88D
C14	CAP CER 0.22UF 16V X7R 0402	1	490-5418-1-ND	GRM155R71C224KA12D
C15	CAP CER 10UF 16V X5R 0805	1	490-3886-1-ND	GRM21BR61C106KE15L
C16	CAP CER 2200PF 630V X7R 1206	1	445-2289-1-ND	C3216X7R2J222K115AA
D1	TVS DIODE 110VWM 177VC DO214AB	1	SMCJ110A-TPMSCT-ND	SMCJ110A-TP
D2	BRIDGE RECT 1PHASE 600V 4A Z4-D	1	641-1502-1-ND	Z4DGP406L-HF
D3	DIODE GEN PURP 800V 1A SMA	1	US1K-FDICT-ND	US1K-13-F
D4	DIODE GEN PURP 200V 200MA SOT23	1	BAS21TPMSCT-ND	BAS21-TP
D5	DIODE ARR SCHOT 30V 200MA SC70-3	1	BAT54SWT1GOSCT-ND	BAT54SWT1G
F1	FUSE BRD MNT 3A 125VAC/VDC 2SMD	1	F1860CT-ND	0452003.NRL
J1, J2, T1	Header, 3-Pin, Three-winding Transformer (Ideal)	3		
L1	CMC 10MH 700MA 2LN TH	1	732-1437-ND	744821110
Q1	30V N-Channel NexFET&#153; Power MOSFET	1	296-27613-1-ND	CSD17312Q5
Q2	MOSFET N-CH 650V 7.3A TO220-3	1	SPP07N60C3XKSA1-ND	SPP07N60C3XKSA1
R1	VARISTOR 470V 6KA DISC 14MM	1	P7222-ND	ERZ-V14D471
R2	RES SMD 51 OHM 5% 1W 2512	1	541-51XCT-ND	CRCW251251R0JNEG
R3, R6	RES 10 OHM 5% 1/16W 0402	2	311-10JRCT-ND	RC0402JR-0710RL
R4	RES SMD 66.5K OHM 1% 1/16W 0402	1	541-66.5KLCT-ND	CRCW040266K5FKED
R5	RES SMD 4.7 OHM 5% 1/4W 1206	1	541-4.7ECT-ND	CRCW12064R70JNEA
R7, R13	RES SMD 0 OHM JUMPER 1/16W 0402	2	541-0.0JCT-ND	CRCW04020000Z0ED
R8	RES SMD 22.6K OHM 1% 1/16W 0402	1	541-22.6KLCT-ND	CRCW040222K6FKED
R9, R15, R19	RES SMD 1K OHM 1% 1/16W 0402	3	541-1.00KLCT-ND	CRCW04021K00FKED
R10	RES SMD 23.2K OHM 1% 1/16W 0402	1	541-23.2KLCT-ND	CRCW040223K2FKED
R11	RES SMD 200K OHM 1% 1/16W 0402	1	541-200KLCT-ND	CRCW0402200KFKED
R12	RES 0.51 OHM 1% 1/2W 1206	1	CRM1206-FX-R510ELFCT-ND	CRM1206-FX-R510ELF
R14, R16	RES SMD 499 OHM 1% 1/16W 0402	2	541-499LCT-ND	CRCW0402499RFKED
R17	RES SMD 2K OHM 1% 1/16W 0402	1	541-2.00KLCT-ND	CRCW04022K00FKED
R18	RES SMD 30.1K OHM 1% 1/16W 0402	1	541-30.1KLCT-ND	CRCW040230K1FKED
R20, R22	RES SMD 10K OHM 1% 1/16W 0402	2	541-10.0KLCT-ND	CRCW040210K0FKED
R21	RES 220K OHM 1% 2W 2512	1	A130749CT-ND	CRGP2512F220K
U1	IC OFFLINE SWITCH FLYBACK 7SOIC	1	296-41059-1-ND	UCC28740DR
U2	IC SECONDARY-SIDE CTRLR 8SON	1	296-28066-1-ND	UCC24610DRBT
U3	OPTOISOLATOR 3.75KV TRANS 4SSOP	1	VOS617A-7X001TCT-ND	VOS617A-7X001T
U4	IC VREF SHUNT ADJ 1% SOT23-3	1	296-17329-1-ND	TL431AIDBZR