



Screen Notes:

- 1 - Stencil Type Framework
- 2 - SIZE (mm) 584x584 mm valid 380x380
- 3 - Stencil Side Top + Bottom on Single Stencil
- 4 - Quantity 1
- 5 - Thickness .12mm
- 6 - Existing Fiducials Half Lasered
- 7 - Electro polishing NO

Notes:

- 1 - Board Type: Panelize by Customer
- 4 - Layers 2 - Top, Bottom
- 5 - PCB Type Normal FR-4 Board
- 6 - TG 130-140
- 7 - Thickness: 1.6mm
- 8 - Min Track/Spacing : 6/6 mil
- 9 - Min Hole Size: .3mm or greater
- 10 - Solder Mask: Green
- 11 - Silkscreen White
- 12 - No Gold Fingers
- 13 - Surface Finish : HASL with lead Click Yes
- 14 - Finish Copper: 1 oz
- 15 - Via Process: Tenting vias

RTC Mod For iPrintSBC7" Display

400350

A1

