



- OUT0 14 VGM0_IN >>> VGM0_IN 8,10
- OUT1 15 VGM1_IN >>> VGM1_IN 8,10
- OUT2 16 VGM2_IN >>> VGM2_IN 8,10
- OUT3 17 VGM3_IN >>> VGM3_IN 8,10
- OUT4 18 VGM4_IN >>> VGM4_IN 8,10
- OUT5 19 VGM5_IN >>> VGM5_IN 8,10
- OUT6 23 VGM6_IN >>> VGM6_IN 8,10
- OUT7 24 VGM7_IN >>> VGM7_IN 8,10
- OUT8 25 VGM8_IN >>> VGM8_IN 8,10
- OUT9 26 VGM9_IN >>> VGM9_IN 8,10
- OUT10 27 VGM10_IN >>> VGM10_IN 8,10
- OUT11 28 VGM11_IN >>> VGM11_IN 8,10
- OUT12 32 VGM12_IN >>> VGM12_IN 8,10
- OUT13 33 VGM13_IN >>> VGM13_IN 8,10
- OUT14 34 VGM14_IN >>> VGM14_IN 8
- OUT15 35 VGM15_IN >>> VGM15_IN 8
- OUT16 36 VGM16_IN >>> VGM16_IN 8
- OUT17 37 VGM17_IN >>> VGM17_IN 8

VGAMMA OUT 100 mA (type)
VCOM OUT 400 mA (type)

