



- ① R14–R17: Required to be 1k.
- ② IC ground should be connected to the 1N cell tab.
- ③ R27 – R31: If smaller resistors are used, user should make sure the power rating of the resistor can handle the desired cell balance current

CHARGER OUTPUT CONTROL 10.5V, 11V, 11.5V, or 12V	
CHGLVL1, CHGLVL0	VOLTAGE
0,0	10.5V
0,1	11V
1,0	11.5V
1,1	12V