

EUT Information

OUT Code: US1280006_AA01
Manufacturer: MUS_BEWHERE_1902
Measured Band & Range: 4G eFDD12 10Mhz TCH 1200Mhz-12750Mhz HORZ - NB-IOT
Test Spec & Test Case 3GPP TS 36.124; 8.2

Final_Result

Frequency (MHz)	RMS (dBm)	Limit (dBm)	Margin (dB)	Meas. Time (ms)	Bandwidth (kHz)	Pol	Azimuth (deg)	Elevation (deg)	Corr. (dB)
1409.960000	-24.42	-30.0	-5.58	3000.0	1000.000	H	37.0	0.0	-107

(continuation of the "Final_Result" table from column 16 ...)

Frequency (MHz)	Comment
1409.960000	16:21:58 - 2019-09-04

Full Spectrum

