

80
00
80
00
00
00
00
00
00
00
00
04
20
08
A0
04
98
02
18
08
18
10
98
20
18
10
A0
00
A0
20
20
40
20
80
20
FF
00
00
04
D4
02
F2
08
10
01
05
C0
55
00
05
00
05
01
00
00
00
00
00
00

0
0
1000
0
0
0
-PULLDOWN -
0
0
0
0
1000
0
0
0
-REFERENCE VOLTAGE -
3.3