



NOTE:-  
F2 to be mount only after the output supply is stable.

LEON CORE SUPPLY = 0.85V/50A MAX

DECAP CH1  
DECAP CH1

4 Nos NEWLY ADDED

SHORT AT A SINGLE POINT

TP\_L\_CORE 0.85V

L\_CORE 0.85V



