

GW INSTEK



Stop



25 Mar 2024
11:52:50

NO Load ← → 1.5A Load

Vin

Vout

FB

COMP

1 RMS 8.30V
1 Max 9.80V

2 RMS 10.5V
2 Max 12.8V

3 RMS 1.02V
3 Max 1.32V

4 RMS 993mV
4 Max 1.56V

1 5V 2 10V 3 1V 4 1V 20ns 0.000s 6.68V DC

Type Edge	Source CH1	Coupling DC	Slope [Icons]	Level 6.68V	Mode Normal	Holdoff 10.0ms
--------------	---------------	----------------	------------------	----------------	----------------	-------------------

NO Load ← → 1.5A Load

Vin

Vout

SS

RES

① RMS 7.92V
① Max 18.8V

② RMS 8.73V
② Max 12.8V

③ RMS 46.7mV
③ Max 168mV

④ RMS 2.16V
④ Max 4.48V

20Hz

20ns 48.88ns

6.48V DC

Coupling
DC AC GND

Impedance
1MΩ

Invert
On Off

Bandwidth
Full

Expand
By Ground

Position /
Set to 0
-5.888V

Probe Voltage
10X

