

OV = 60V
UVLO = 12V
Current Limit ILIM = 62A
OVC TMR = 1ms
Auto-Retry after Fault = 1.5s

VNominal = 48V INominal = 30A

VIN = 12V to 60V IMAX = 60A

30A capacity per MOSFET stage

PSMN2R3-100SSEJ T_{J,DC} max = 175°C.
Estimated 118 °C at IMAX with 2 Mosfet

InRUSH = 0.53A
dv/dt = 0.81V/ms
T = 60ms to Vout Nominal

TP106
GND_OR

