



20.0ms 50.0kS/s 1 / 1.20 V
 0.000000 s 10k points

	Value	Mean	Min	Max	Std Dev
Frequency	9.68 V	12.2	-6.13m	14.9	3.56
	240.4 Hz	Low signal amplitude			
	11.1 V	13.5	300m	15.3	2.85

Save Waveform
Save Setup
Recall Waveform
Recall Setup
Assign **Save** to **Waveform**