



Comment	Description	Designator	Footprint	LibRef	Quantity
PCB-5M5	Battery端子	BATT-?, Pack-?	PCB-5M5	PCB-5M5	2
0.1uF/50V		C?	C0603	CAP	3
0.1uF/100V		C?	C1206 - duplicate	CAP	2
1uF/50V	1uF/50V, [NoValue]	C?	C0603	CAP	19
1uF/50V		C?	C0805 - duplicate	CAP	3
NC		C?	C0603	CAP	2
CON16	Connector	CON?	S12B-PH-SM3-TB	CON16	2
BAV16W	Schottky Diode	D?	SOD-123	DIODE SCHOTTKY	3
3V		DZ?	SOD-123	ZD	1
16V		DZ?	SOD-123	ZD	1
BQ77915		IC?		BQ77915	3
TS1	Header, 2-Pin	P?	HDR1X2	Header 2	1
TS2	Header, 2-Pin	P?	HDR1X2	Header 2	1
TS3	Header, 2-Pin	P?	HDR1X2	Header 2	1
FDN340P		Q?		MOSFET P	1
MOSFET N		Q?		MOSFET N	8
MOSFET N		Q?	SOT23-Ken	MOSFET N	15
0		R?	R0603	RES1	6
0.002		R?	R0603	RES1	2
1K	1K, [NoValue]	R?	R0603	RES1	3
1M		R?	R0603	RES1	3
2.2K		R?	R0603	RES1	1
5.1K		R?	R0603	RES1	1
5.1M		R?	R0603	RES1	1
10K		R?	R0603	RES1	9
10M		R?	R0603	RES1	8
33	33, 333, [NoValue]	R?	R0603	RES1	16
100		R?	R0603	RES1	2
100K		R?	R0603	RES1	1
200		R?	R2512	RES1	2
220		R?	R0603	RES1	8
450K		R?	R0603	RES1	3
N.R	N.R	R?	R0603	RES1	4
NR		R?	R0603	RES1	5
NR		R?	R1206-Ken	RES1	15