

输出48V/2.5A(120W)，效率90%，电感22uH，开关频率530k

	正常电压	关机电压
输入电压	24V	20.66V
输入电流	5.6A	6.3A
电感峰值电流	6.1A	6.64A
限流(120%)	7.32A	7.97A
限流电阻	电阻10mR，限流7.5A，峰值功率需求0.73W 电阻7mR，限流10.7A，峰值功率需求1.09W R2010=3/4W，R2312=1W	

