

CSD18532NQ5B Transfer Data

125C		25C		-55C	
Vgs	Id	Vgs	Id	Vgs	Id
0	0	0	0	0	0
1.51	0.00001	2.355	0.00001	2.875	0.00001
1.75	0.00005	2.513	0.00005	2.987	0.00005
1.85	0.0001	2.581	0.0001	3.035	0.0001
2.092	0.0005	2.738	0.0005	3.150	0.0005
2.195	0.001	2.806	0.001	3.200	0.001
2.296	0.002	2.874	0.002	3.252	0.002
2.428	0.005	2.966	0.005	3.322	0.005
2.526	0.01	3.037	0.01	3.377	0.01
2.757	0.05	3.206	0.05	3.512	0.05
2.857	0.1	3.282	0.1	3.574	0.1
2.96	0.2	3.362	0.2	3.641	0.2
3.102	0.5	3.474	0.5	3.736	0.5
3.213	1	3.563	1	3.809	1
3.338	2	3.666	2	3.898	2
3.522	5	3.82	5	4.032	5
3.681	10	3.953	10	4.148	10
3.878	20	4.119	20	4.294	20
4.321	60	4.505	60	4.634	60
4.481	80	4.648	80	4.763	80
4.637	100	4.8	100	4.903	100
4.766	120	4.91	120	5.005	120
4.892	140	5.017	140	5.105	140
5.015	160	5.12	160	5.200	160
5.136	180	5.22	180	5.285	180
5.257	200	5.32	200	5.371	200

CSD18532NQ5B Transfer Data

